



THORNE & Thorne & Derrick

DERRICK +44 (0) 191 490 1547

INTERNATIONAL www.heatingandprocess.com

# **INDOOR AIR QUALITY** DATA LOGGER

- Measures and logs CO<sub>2</sub>, relative humidity and temperature
- ROTRONIC HYGROMER® IN-1 humidity sensor
- 40,000 data point memory for CO<sub>2</sub>, humidity and temperature values
- Maximum, minimum and average values displayed
- Adjustable audible and visual CO<sub>2</sub> alarm
- Optional external temperature probe
- Includes software for configuration and data download







Thorne & Derrick RICK +44 (0) 191 490 1547 www.heatingandprocess.com



# **CL11**

# **BE PRECISE:** THE MAIN ADVANTAGES AT A GLANCE

The CL11 benchtop display unit is the latest development of an inexpensive multiple parameter meter that simultaneously measures and records CO2, humidity and temperature. Equipped with the field-tested ROTRONIC HYGROMER® IN-1 humidity sensor, this instrument offers unbeatable value for money. Using the ROTRONIC software package SW21, it can be easily set to record as required and data can then be downloaded, saved and analyzed.

## **Sensors / Calibration**

- HYGROMER® IN-1 humidity sensor
- Calibration of humidity sensor at 35/80 %RH
- Automatic CO<sub>2</sub> calibration and manually at 400 ppm

#### **Data logging function**

- 40,000 data point memory for CO<sub>2</sub>, humidity and temperature values
- Data download using the included ROTRONIC Software SW21 or with the optional HW4 Software

#### **Connections**

- Mini USB port for connection to a PC
- 5 VDC power supply connector for the included AC adapter

#### CO<sub>2</sub> alarm

• Adjustable audible CO<sub>2</sub> alarm

# Large display

· With backlight

## **Controls**

• Large buttons for easy operation

# **Temperature probe**

• External temperature probe AC1215 (optional)





Thorne & Derrick **DERRICK** +44 (0) 191 490 1547 INTERNATIONAL www.heatingandprocess.com



# THORNE & Thorne & Derrick DERRICK +44 (0) 191 490 1547 INTERNATIONAL www.heatingandprocess.com

# **APPLICATIONS**







Indoor air quality

# **PRINCIPLES**

The CL11 data logger evaluates air quality with the combined measurements of CO<sub>2</sub>, humidity, and temperature. These measurements are important to understand Indoor Air Quality (IAQ) in classrooms, conference and waiting rooms, as well as any indoor areas where people gather. A high concentration of carbon dioxide can develop quickly when closed rooms with insufficient ventilation are filled with people.

Carbon dioxide  $(CO_2)$  is a colorless and odorless gas that exists in the earth's atmosphere and which is dangerous in high concentrations. The proportion of  $CO_2$  in natural ambient air is about 0.04% or 400 ppm. Exhaled air contains approximately 3.8% by volume  $CO_2$ , which quickly mixes with the ambient air. When closed rooms are insufficiently ventilated, the levels of  $CO_2$  increase quickly leading to fatigue and loss of concentration for the rooms occupants. In order to initiate improvements to the air quality, for example by increasing the supply of fresh air, it is important to measure the key parameters of indoor air quality. These parameters are  $CO_2$ , humidity, and temperature.

# Guidelines

350 - 450 ppm	400 - 1,200 ppm	>1,000 ppm	5,000 ppm (0.5%vol)	38,000 ppm (3.8%vol)	>100,000 ppm (10%vol)
Fresh air outdoors	Room air	Fatigue and loss of concentration become apparent	Maximum permissible value at the workplace during an 8-hour workday	Breathing air (direct exhalation)	Nausea, vomiting, loss of consciousness and death




Thorne & Derrick


DERRICK +44 (0) 191 490 1547


ITERNATIONAL www.heatingandprocess.com

# **TECHNICAL INFORMATION**

## **Dimensions**







# Suitable accessories

Art. no. Description
ER-15 Humidity calibration device
EA35-SCS Humidity standard 35 %RH
EA80-SCS Humidity standard 80 %RH
AC1215 External temperature probe

### Included

- 1 CL11 data logger
- 1 AC adapter AC1214
- 1 ROTRONIC software SW2.x

General			
Parameters	CO <sub>2</sub> , relative humidity and temperature		
Range of application	050 °C / 0100 %RH, non-condensing		
Power supply	Via AC1214 AC adapter (included in the delivery package)		
IP protection	IP30		
Clock	Real time clock with 2 min. battery backup		
Alarm	Adjustable for CO <sub>2</sub> measurement		
Technical information/Functi	ions		
Current consumption	50 mA		
Warm-up time	<1 min.		
Memory capacity	40,000 values with time stamp, automatic recording (%RH / °C / CO <sub>2</sub> / external temperature probe)		
CO <sub>2</sub> measurement			
Measurement principle	Non dispersive infrared (NDIR) with automatic baseline correction (ABC)		
Measurement range	05,000 ppm		
Accuracy at 23 °C ±5 K	±30 ppm ±5 % of the measured value		
Response time	<10 sec @ 30 cc/min. flow, <3 min diffusion time		
Adjustment point	Automatic calibration, manual calibration at 400 ppm		
Pressure dependence	+1.6 % reading per kPa		
Null drift	<10 ppm/year		
Maintenance	No maintenance (standard indoor application)		
Humidity measurement	no mamenance (standard moor application)		
Humidity sensor	ROTRONIC HYGROMER® IN-1		
Measurement range	0100 %RH		
Accuracy at 23 °C ±5 K	<2.5 %RH (1090 %RH)		
Adjustment points	35, 80 %RH		
Response time τ63	<30 s, without filter		
Long-term stability	<1.5 %RH / year		
Temperature measurement	11.5 Mility year		
Sensor	Thermistor		
Measurement range	-2060 °C		
Accuracy at 23 °C ±5 K	±0.3 °K		
Response time	4 s		
Conformities / Housing	[ 17		
CE / EMC compatibility	EMC DIRECTIVE 2004/108/EC, standard EN61326-1:2006		
Housing material	ABS		
Dimensions	157 x 120 x 45 mm		
Weight	Approx. 200 g		
	ROTRONIC SW21 free of charge, HW4 subject to charge		

External temperature probe AC1215 (available as optional extra)			
Sensor	Thermistor		
Measurement range	-2070 °C		
Accuracy	±0.6 °C @ 540 °C, ±1.0 °C rest of range		
Material of probe	Stainless steel		
Material of handle	PVC		
Probe dimensions	Ø 3.8 x 100 mm		
Handle dimensions	Ø12.3 x74 mm		
Cable length	116 cm		
Connector	Jack plug Ø 2.5 x 11 mm		



Thorne & Derrick

TIONAL +44 (0) 191 490 1547

www.heatingandprocess.com